



OmniAire 800PAC

Omnitec Design, Manufacturing Air Purification Equipment Since 1988

The **OmniAire Portable Air Cleaner (PAC)** machine with 99.99% HEPA and UVGI germicidal lights eliminates sub-micron particulates and microbial contamination. Designed for healthcare environments, it offers quiet operation as the air is exhausted through the HEPA filter. This unit has fully adjustable air flow and a small footprint.

OmniAire 800 PAC is used for:

- Air Purification and Sterilization in Healthcare**
- Veterinary Clinics**
- Hospital Pharmacies - USP 797 Requirements**
- First Response Shelters, Mobile Hospitals**
- Laboratories, Clean Rooms**
- Isolation Rooms - Positive or Negative Room Pressurization**
- Morgues & Mortuaries**
- Archives**



OmniAire 800PAC Specifications:

- Air flow:** 100 to 600 cfm with variable speed control
- Filtration:** Primary Filter - 65% Pleated Filter
HEPA Filter - 99.99%, 0.3 μ , metal frame, 12"x12"x12", individually tested and Certified
- Power:** 115 Volts, 60 Hz, 3.5 amp maximum
- Controls:** Recessed panel with Variable Speed Control
Differential pressure indicator, 0-3" WC to indicate HEPA filter loading;
Hour meter with LCD display;
UVGI lights ON/OFF switch and lamps/ballast status LED lights;
- Construction:** Aluminum Housing with Galvanized Metal reinforcements, riveted and silicone sealed
- Size:** 15" x 15" x 36" high, 3" hospital grade casters
- Weight:** 70 lbs.
- Connections:** Inlet with 12"x12" pleated filter and protective screen. Discharge on top through HEPA and protective screen

ORDERING INFO	PART #
OmniAire 800PAC.....	OA800PAC
HEPA Filter 99.99%, 0.3 μ	MFH1212G
Primary Pleated Filter.....	OPF12
Connection Adapter, 8"	MFIM8
Quick Clamp, 8"	QC8
Flexible Duct, 8"x25'	MD8
OdorGuard 600 Carbon Filter	OG1212
OdorGuard 750 Plus Carbon Filter	OGP1212

Optional accessories:

- Connection adapter for 8" diameter flex hose on the discharge and/or suction side
- OdorGuard 600 high capacity carbon fiber filter
- OdorGuard 750 high capacity carbon/alumina fiber filter



Note:

- OmniAire 800 PAC can be ordered to operate on 230 VAC/60-50 Hz
- Also available with a 99.99% @ 0.1-0.2 μ HEPA Filter



CONFORMS TO UL STD 507
CERTIFIED TO CAN/CSA STD
C22.2 NO. 113-M1984

3067108

www.omnitecdesign.com
2125 196th Street SW, Suite 115, Lynnwood, WA 98036
phone 425-774-3257 fax 425-774-4983